

Audio Shade - Clicks

No.	Description	Duration
1	BUTTON METALLIC Avid Omni (rack-mounted) - Click Rapid - Distant - 4X	00:08.500
2	BUTTON METALLIC Avid Omni (rack-mounted) - Click Rapid - Near - 4X	00:08.500
3	BUTTON METALLIC Avid Omni (rack-mounted) - Click Single - Distant - 8X	00:12.000
4	BUTTON METALLIC Avid Omni (rack-mounted) - Click Single - Near - 8X	00:12.000
5	BUTTON METALLIC Bellari Tube Phono Preamp VP-130 - Click Double - Distant - 12X	00:17.581
6	BUTTON METALLIC Bellari Tube Phono Preamp VP-130 - Click Double - Near - 12X	00:17.581
7	BUTTON METALLIC Bellari Tube Phono Preamp VP-130 - Click Single Hard - Distant - 6X	00:09.158
8	BUTTON METALLIC Bellari Tube Phono Preamp VP-130 - Click Single Hard - Near - 6X	00:09.158
9	BUTTON METALLIC Bellari Tube Phono Preamp VP-130 - Click Single Soft - Distant - 4X	00:05.759
10	BUTTON METALLIC Bellari Tube Phono Preamp VP-130 - Click Single Soft - Near - 4X	00:05.759
11	BUTTON PLASTIC Amplifier Peavey Classic 30 - Click Rapid - Distant - 5X	00:06.725
12	BUTTON PLASTIC Amplifier Peavey Classic 30 - Click Rapid - Near - 5X	00:06.725
13	BUTTON PLASTIC Amplifier Peavey Classic 30 - Click Single Hard - Distant - 4X	00:05.179
14	BUTTON PLASTIC Amplifier Peavey Classic 30 - Click Single Hard - Near - 4X	00:05.179
15	BUTTON PLASTIC Apple iPhone 6 Home Button - Click Rapid Hard - Distant - 5X	00:05.400
16	BUTTON PLASTIC Apple iPhone 6 Home Button - Click Rapid Hard - Near - 5X	00:05.400
17	BUTTON PLASTIC Apple iPhone 6 Home Button - Click Single Hard - Distant - 14X	00:13.658
18	BUTTON PLASTIC Apple iPhone 6 Home Button - Click Single Hard - Near - 14X	00:13.658
19	BUTTON PLASTIC Apple iPhone 6 Home Button - Click Single Soft - Distant - 16X	00:16.000
20	BUTTON PLASTIC Apple iPhone 6 Home Button - Click Single Soft - Near - 16X	00:16.000
21	BUTTON PLASTIC Apple iPhone 6 Volume Adjustment - Click Rapid - Distant - 4X	00:05.145
22	BUTTON PLASTIC Apple iPhone 6 Volume Adjustment - Click Rapid - Near - 4X	00:05.145
23	BUTTON PLASTIC Apple iPhone 6 Volume Adjustment - Click Single - Distant - 7X	00:06.661
24	BUTTON PLASTIC Apple iPhone 6 Volume Adjustment - Click Single - Near - 7X	00:06.661
25	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Slam - Click Various Hard - Distant - 5X	00:19.000
26	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Slam - Click Various Hard - Near - 5X	00:19.000
27	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Stroke - Click Single Hard - Distant - 16X	00:16.000
28	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Stroke - Click Single Hard - Near - 16X	00:16.000
29	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Stroke - Click Single Medium - Distant - 20X	00:19.500
30	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Stroke - Click Single Medium - Near - 20X	00:19.500
31	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Stroke - Click Single Soft - Distant - 18X	00:17.500
32	BUTTON PLASTIC Keyboard Apple Laptop [2011] Key Stroke - Click Single Soft - Near - 18X	00:17.500
33	BUTTON PLASTIC Keyboard Apple Laptop [2011] Space Bar Stroke - Click Single Hard - Distant - 11X	00:11.000
34	BUTTON PLASTIC Keyboard Apple Laptop [2011] Space Bar Stroke - Click Single Hard - Near - 11X	00:11.000
35	BUTTON PLASTIC Keyboard Apple Laptop [2011] Space Bar Stroke - Click Single Medium - Distant - 7X	00:07.000
36	BUTTON PLASTIC Keyboard Apple Laptop [2011] Space Bar Stroke - Click Single Medium - Near - 7X	00:07.000
37	BUTTON PLASTIC Keyboard Apple Laptop [2011] Space Bar Stroke - Click Single Soft - Distant - 13X	00:13.000
38	BUTTON PLASTIC Keyboard Apple Laptop [2011] Space Bar Stroke - Click Single Soft - Near - 13X	00:13.000
39	BUTTON PLASTIC Keyboard Apple Laptop [2011] - Type Fast Paced Aggressive - Distant - Long	01:18.425
40	BUTTON PLASTIC Keyboard Apple Laptop [2011] - Type Fast Paced Aggressive - Near - Long	01:18.425
41	BUTTON PLASTIC Keyboard Apple Laptop [2011] - Type Fast Paced Soft - Distant - Long	00:50.290
42	BUTTON PLASTIC Keyboard Apple Laptop [2011] - Type Fast Paced Soft - Near - Long	00:50.290
43	BUTTON PLASTIC Blender - Click Single Hard - Distant - 10X	00:10.500
44	BUTTON PLASTIC Blender - Click Single Hard - Near - 10X	00:10.500
45	BUTTON PLASTIC Blender - Click Single Soft - Distant - 9X	00:09.500
46	BUTTON PLASTIC Blender - Click Single Soft - Near - 9X	00:09.500
47	BUTTON PLASTIC Boombox Sony CFS DW-34 Pause - Click Rapid Hard - Distant - 6X	00:11.000
48	BUTTON PLASTIC Boombox Sony CFS DW-34 Pause - Click Rapid Hard - Near - 6X	00:11.000

Audio Shade - Clicks

49	BUTTON PLASTIC Boombox Sony CFS DW-34 Pause - Click Single Hard - Distant - 6X	00:08.500
50	BUTTON PLASTIC Boombox Sony CFS DW-34 Pause - Click Single Hard - Near - 6X	00:08.500
51	BUTTON PLASTIC Boombox Sony CFS DW-34 Pause - Click Single Soft - Distant - 10X	00:14.500
52	BUTTON PLASTIC Boombox Sony CFS DW-34 Pause - Click Single Soft - Near - 10X	00:14.500
53	BUTTON PLASTIC Boombox Sony CFS DW-34 Play - Click Single Hard - Distant - 7X	00:13.500
54	BUTTON PLASTIC Boombox Sony CFS DW-34 Play - Click Single Hard - Near - 7X	00:13.500
55	BUTTON PLASTIC Boombox Sony CFS DW-34 Play - Click Single Soft - Distant - 9X	00:17.500
56	BUTTON PLASTIC Boombox Sony CFS DW-34 Play - Click Single Soft - Near - 9X	00:17.500
57	BUTTON PLASTIC Fire Alarm - Click Single - Distant - 12X	00:18.000
58	BUTTON PLASTIC Fire Alarm - Click Single - Near - 12X	00:18.000
59	BUTTON PLASTIC Flashlight Defiant - Click Double - Distant - 4X	00:05.626
60	BUTTON PLASTIC Flashlight Defiant - Click Double - Near - 4X	00:05.868
61	BUTTON PLASTIC Flashlight Defiant - Click Hard - Distant - 11X	00:16.027
62	BUTTON PLASTIC Flashlight Defiant - Click Hard - Near - 11X	00:16.288
63	BUTTON PLASTIC Flashlight Defiant - Click Rapid - Distant - 1X	00:01.832
64	BUTTON PLASTIC Flashlight Defiant - Click Rapid - Near - 1X	00:02.153
65	BUTTON PLASTIC Flashlight Defiant - Click Single Slow - Distant - 2X	00:03.217
66	BUTTON PLASTIC Flashlight Defiant - Click Single Slow - Near - 2X	00:03.551
67	BUTTON PLASTIC Flashlight Defiant - Click - Distant - 7X	00:09.873
68	BUTTON PLASTIC Flashlight Defiant - Click - Near - 7X	00:10.000
69	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Double - Distant - 6X	00:05.500
70	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Double - Near - 6X	00:05.500
71	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Rapid - Distant - 5X	00:10.000
72	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Rapid - Near - 5X	00:10.000
73	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Single Hard - Distant - 13X	00:12.500
74	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Single Hard - Near - 13X	00:12.500
75	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Single - Distant - 10X	00:09.500
76	BUTTON PLASTIC Gadget Small Crisp (mouse-like) - Click Single - Near - 10X	00:09.500
77	BUTTON PLASTIC Game Controller Playstation 4 Button - Click Rapid Mash Hard - Distant - Long	00:17.454
78	BUTTON PLASTIC Game Controller Playstation 4 Button - Click Rapid Mash Hard - Near - Long	00:17.454
79	BUTTON PLASTIC Game Controller Playstation 4 Button - Click Single Soft - Distant - 15X	00:15.000
80	BUTTON PLASTIC Game Controller Playstation 4 Button - Click Single Soft - Near - 15X	00:15.000
81	BUTTON PLASTIC Game Controller Playstation 4 Joystick - Click Rapid Mash Hard - Distant - 5X	00:07.000
82	BUTTON PLASTIC Game Controller Playstation 4 Joystick - Click Rapid Mash Hard - Near - 5X	00:07.000
83	BUTTON PLASTIC Game Controller Playstation 4 Joystick - Click Single Hard - Distant - 12X	00:12.000
84	BUTTON PLASTIC Game Controller Playstation 4 Joystick - Click Single Hard - Near - 12X	00:12.000
85	BUTTON PLASTIC Game Controller Playstation 4 Joystick - Click Single Soft - Distant - 8X	00:08.000
86	BUTTON PLASTIC Game Controller Playstation 4 Joystick - Click Single Soft - Near - 8X	00:08.000
87	BUTTON PLASTIC Hard-Drive Nexstar CX - Click Single Hard On Off - Distant - 10X	00:10.000
88	BUTTON PLASTIC Hard-Drive Nexstar CX - Click Single Hard On Off - Near - 10X	00:10.000
89	BUTTON PLASTIC Hard-Drive Nexstar CX - Click Single Soft On Off - Distant - 11X	00:11.000
90	BUTTON PLASTIC Hard-Drive Nexstar CX - Click Single Soft On Off - Near - 11X	00:11.000
91	BUTTON PLASTIC Intervalometer Canon RS-60E3 - Click Rapid - Distant - 6X	00:12.702
92	BUTTON PLASTIC Intervalometer Canon RS-60E3 - Click Rapid - Near - 6X	00:12.702
93	BUTTON PLASTIC Intervalometer Canon RS-60E3 - Click Single Hard - Distant - 8X	00:08.000
94	BUTTON PLASTIC Intervalometer Canon RS-60E3 - Click Single Hard - Near - 8X	00:08.000
95	BUTTON PLASTIC Intervalometer Canon RS-60E3 - Click Single Soft - Distant - 7X	00:07.000
96	BUTTON PLASTIC Intervalometer Canon RS-60E3 - Click Single Soft - Near - 7X	00:07.000
97	BUTTON PLASTIC Label Maker - Click Rapid - Distant - 8X	00:16.000

Audio Shade - Clicks

98	BUTTON PLASTIC Label Maker - Click Rapid - Near - 8X	00:16.000
99	BUTTON PLASTIC Label Maker - Click Single Hard - Distant - 6X	00:09.500
100	BUTTON PLASTIC Label Maker - Click Single Hard - Near - 6X	00:09.500
101	BUTTON PLASTIC Label Maker - Click Single Soft - Distant - 12X	00:18.000
102	BUTTON PLASTIC Label Maker - Click Single Soft - Near - 12X	00:18.000
103	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Double Hard - Distant - 4X	00:03.855
104	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Double Hard - Near - 4X	00:03.855
105	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Double Soft - Distant - 5X	00:05.040
106	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Double Soft - Near - 5X	00:05.040
107	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Rapid - Distant - 6X	00:10.393
108	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Rapid - Near - 6X	00:10.393
109	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Single Hard - Distant - 14X	00:13.842
110	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Single Hard - Near - 14X	00:13.842
111	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Single Soft - Distant - 7X	00:06.821
112	BUTTON PLASTIC MOUSE Apple Magic Mouse - Click Single Soft - Near - 7X	00:06.821
113	BUTTON PLASTIC MOUSE Apple Magic Mouse (wooden surface) - Click Double Soft - Distant - 15X	00:15.500
114	BUTTON PLASTIC MOUSE Apple Magic Mouse (wooden surface) - Click Double Soft - Near - 15X	00:15.500
115	BUTTON PLASTIC MOUSE Apple Magic Mouse (wooden surface) - Click Rapid - Distant - 6X	00:11.500
116	BUTTON PLASTIC MOUSE Apple Magic Mouse (wooden surface) - Click Rapid - Near - 6X	00:11.500
117	BUTTON PLASTIC MOUSE Apple Magic Mouse (wooden surface) - Click Single Soft - Distant - 12X	00:12.000
118	BUTTON PLASTIC MOUSE Apple Magic Mouse (wooden surface) - Click Single Soft - Near - 12X	00:12.000
119	BUTTON PLASTIC MOUSE Handshoe - Click Double Soft - Distant - 10X	00:10.000
120	BUTTON PLASTIC MOUSE Handshoe - Click Double Soft - Near - 10X	00:10.000
121	BUTTON PLASTIC MOUSE Handshoe - Click Rapid Hard - Distant - 6X	00:11.500
122	BUTTON PLASTIC MOUSE Handshoe - Click Rapid Hard - Near - 6X	00:11.500
123	BUTTON PLASTIC MOUSE Handshoe - Click Single Hard - Distant - 8X	00:08.000
124	BUTTON PLASTIC MOUSE Handshoe - Click Single Hard - Near - 8X	00:08.000
125	BUTTON PLASTIC MOUSE Handshoe - Click Single Soft - Distant - 9X	00:09.000
126	BUTTON PLASTIC MOUSE Handshoe - Click Single Soft - Near - 9X	00:09.000
127	BUTTON PLASTIC MOUSE Handshoe (wooden surface) - Click Rapid Hard - Distant - 3X	00:05.613
128	BUTTON PLASTIC MOUSE Handshoe (wooden surface) - Click Rapid Hard - Near - 3X	00:05.613
129	BUTTON PLASTIC MOUSE Handshoe (wooden surface) - Click Single Hard - Distant - 13X	00:12.738
130	BUTTON PLASTIC MOUSE Handshoe (wooden surface) - Click Single Hard - Near - 13X	00:12.738
131	BUTTON PLASTIC MOUSE Handshoe (wooden surface) - Click Single Soft - Distant - 8X	00:08.000
132	BUTTON PLASTIC MOUSE Handshoe (wooden surface) - Click Single Soft - Near - 8X	00:08.000
133	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode - Click Rapid - Distant - 6X	00:12.000
134	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode - Click Rapid - Near - 6X	00:12.000
135	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode - Click Single Hard - Distant - 12X	00:12.000
136	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode - Click Single Hard - Near - 12X	00:12.000
137	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode - Click Single Soft - Distant - 8X	00:11.500
138	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode - Click Single Soft - Near - 8X	00:11.500
139	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode (wooden surface) - Click Rapid Hard - Distant - 5X	00:13.500
140	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode (wooden surface) - Click Rapid Hard - Near - 5X	00:13.500
141	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode (wooden surface) - Click Single Hard - Distant - 8X	00:08.000
142	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode (wooden surface) - Click Single Hard - Near - 8X	00:08.000
143	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode (wooden surface) - Click Single Soft - Distant - 10X	00:09.856
144	BUTTON PLASTIC MOUSE Logitech M720 Scroll Wheel Mode (wooden surface) - Click Single Soft - Near - 10X	00:09.856
145	BUTTON PLASTIC MOUSE Logitech M720 - Click Double Hard - Distant - 14X	00:14.000
146	BUTTON PLASTIC MOUSE Logitech M720 - Click Double Hard - Near - 14X	00:14.000

Audio Shade - Clicks

147	BUTTON PLASTIC MOUSE Logitech M720 - Click Double Soft - Distant - 13X	00:13.000
148	BUTTON PLASTIC MOUSE Logitech M720 - Click Double Soft - Near - 13X	00:13.000
149	BUTTON PLASTIC MOUSE Logitech M720 - Click Rapid Hard - Distant - 6X	00:15.500
150	BUTTON PLASTIC MOUSE Logitech M720 - Click Rapid Hard - Near - 6X	00:15.500
151	BUTTON PLASTIC MOUSE Logitech M720 - Click Single Hard - Distant - 10X	00:09.960
152	BUTTON PLASTIC MOUSE Logitech M720 - Click Single Hard - Near - 10X	00:09.960
153	BUTTON PLASTIC MOUSE Logitech M720 - Click Single Soft - Distant - 7X	00:07.000
154	BUTTON PLASTIC MOUSE Logitech M720 - Click Single Soft - Near - 7X	00:07.000
155	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Double Hard - Distant - 12X	00:11.829
156	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Double Hard - Near - 12X	00:11.829
157	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Double Soft - Distant - 11X	00:10.639
158	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Double Soft - Near - 11X	00:10.639
159	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Rapid Hard - Distant - 5X	00:14.583
160	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Rapid Hard - Near - 5X	00:14.583
161	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Single Hard - Distant - 12X	00:12.000
162	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Single Hard - Near - 12X	00:12.000
163	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Single Soft - Distant - 10X	00:10.000
164	BUTTON PLASTIC MOUSE Logitech M720 (wooden surface) - Click Single Soft - Near - 10X	00:10.000
165	BUTTON PLASTIC Pen Ballpoint - Click Rapid - Distant - 5X	00:16.000
166	BUTTON PLASTIC Pen Ballpoint - Click Rapid - Near - 5X	00:16.000
167	BUTTON PLASTIC Pen Ballpoint - Click Single Hard - Distant - 11X	00:11.000
168	BUTTON PLASTIC Pen Ballpoint - Click Single Hard - Near - 11X	00:11.000
169	BUTTON PLASTIC Pen Ballpoint - Click Single - Distant - 8X	00:12.500
170	BUTTON PLASTIC Pen Ballpoint - Click Single - Near - 8X	00:12.500
171	BUTTON PLASTIC Remote Control - Click Rapid Distant - 7X	00:14.615
172	BUTTON PLASTIC Remote Control - Click Rapid Near - 7X	00:14.615
173	BUTTON PLASTIC Remote Control - Click Single Hard Distant - 9X	00:09.000
174	BUTTON PLASTIC Remote Control - Click Single Hard Near - 9X	00:09.000
175	BUTTON PLASTIC Remote Control - Click Single Soft Distant - 11X	00:11.000
176	BUTTON PLASTIC Remote Control - Click Single Soft Near - 11X	00:11.000
177	BUTTON PLASTIC Springy - Click Single Hard - Distant - 8X	00:12.000
178	BUTTON PLASTIC Springy - Click Single Hard - Near - 8X	00:12.000
179	BUTTON PLASTIC Springy - Click Single Soft - Distant - 13X	00:25.500
180	BUTTON PLASTIC Springy - Click Single Soft - Near - 13X	00:25.500
181	BUTTON PLASTIC Vinyl Player Stanton T80 RPM Toggle - Click Rapid - Distant - 13X	00:18.000
182	BUTTON PLASTIC Vinyl Player Stanton T80 RPM Toggle - Click Rapid - Near - 13X	00:18.000
183	BUTTON PLASTIC Vinyl Player Stanton T80 RPM Toggle - Click Single Hard - Distant - 5X	00:07.000
184	BUTTON PLASTIC Vinyl Player Stanton T80 RPM Toggle - Click Single Hard - Near - 5X	00:07.000
185	BUTTON PLASTIC Vinyl Player Stanton T80 RPM Toggle - Click Single Soft - Distant - 10X	00:14.500
186	BUTTON PLASTIC Vinyl Player Stanton T80 RPM Toggle - Click Single Soft - Near - 10X	00:14.500
187	BUTTON PLASTIC Vinyl Player Stanton T80 Start Stop - Click Rapid - Distant - 5X	00:08.021
188	BUTTON PLASTIC Vinyl Player Stanton T80 Start Stop - Click Rapid - Near - 5X	00:08.021
189	BUTTON PLASTIC Vinyl Player Stanton T80 Start Stop - Click Single Hard - Distant - 7X	00:07.952
190	BUTTON PLASTIC Vinyl Player Stanton T80 Start Stop - Click Single Hard - Near - 7X	00:07.952
191	BUTTON PLASTIC Vinyl Player Stanton T80 Start Stop - Click Single Soft - Distant - 9X	00:13.000
192	BUTTON PLASTIC Vinyl Player Stanton T80 Start Stop - Click Single Soft - Near - 9X	00:13.000
193	DIAL PLASTIC Hair Trimmer - Click Rapid - Distant - 18X	00:29.093
194	DIAL PLASTIC Hair Trimmer - Click Rapid - Near - 18X	00:29.093
195	DIAL PLASTIC Hair Trimmer - Click Single - Distant - 7X	00:10.141

Audio Shade - Clicks

196	DIAL PLASTIC Hair Trimmer - Click Single - Near - 7X	00:10.141
197	DIAL PLASTIC Iron - Click Long Burst Various - Distant - 14X (Good for scope zoom cheat)	00:33.000
198	DIAL PLASTIC Iron - Click Long Burst Various - Near - 14X (Good for scope zoom cheat)	00:33.000
199	DIAL PLASTIC Iron - Click Short Burst Various - Distant - 14X (Good for scope zoom cheat)	00:14.000
200	DIAL PLASTIC Iron - Click Short Burst Various - Near - 14X (Good for scope zoom cheat)	00:14.000
201	DIAL PLASTIC Iron - Click Single - Distant - 15X (Good for clock timer cheat)	00:07.500
202	DIAL PLASTIC Iron - Click Single - Near - 15X (Good for clock timer cheat)	00:07.500
203	PUMP PLASTIC Oxo Food Chopper - Press Double Hard - Distant - 8X	00:09.192
204	PUMP PLASTIC Oxo Food Chopper - Press Double Hard - Near - 8X	00:09.192
205	PUMP PLASTIC Oxo Food Chopper - Press Double Soft - Distant - 11X	00:18.070
206	PUMP PLASTIC Oxo Food Chopper - Press Double Soft - Near - 11X	00:18.070
207	PUMP PLASTIC Oxo Food Chopper - Press Rapid Fast - Distant - 4X	00:15.266
208	PUMP PLASTIC Oxo Food Chopper - Press Rapid Fast - Near - 4X	00:15.266
209	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Double Hard - Distant - 8X	00:14.423
210	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Double Hard - Near - 8X	00:14.423
211	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Double Soft - Distant - 5X	00:12.847
212	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Double Soft - Near - 5X	00:12.847
213	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Single Hard - Distant - 10X	00:14.010
214	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Single Hard - Near - 10X	00:14.010
215	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Single Soft - Distant - 12X	00:21.120
216	PUMP PLASTIC Oxo Food Chopper (wooden surface) - Press Single Soft - Near - 12X	00:21.120
217	PUMP PLASTIC Iron Water Spray - Click Rapid - Distant - 3X	00:10.500
218	PUMP PLASTIC Iron Water Spray - Click Rapid - Near - 3X	00:10.500
219	PUMP PLASTIC Iron Water Spray - Click Single Slow - Distant - 7X	00:10.500
220	PUMP PLASTIC Iron Water Spray - Click Single Slow - Near - 7X	00:10.500
221	PUMP PLASTIC Iron Water Spray - Click Single - Distant - 7X	00:10.320
222	PUMP PLASTIC Iron Water Spray - Click Single - Near - 7X	00:10.320
223	SWITCH METALLIC Amplifier Peavey Classic 30 (back of cab) - Click Single Hard - Distant - 8X	00:15.097
224	SWITCH METALLIC Amplifier Peavey Classic 30 (back of cab) - Click Single Hard - Near - 8X	00:15.097
225	SWITCH METALLIC Amplifier Peavey Classic 30 (back of cab) - Click Single Soft - Distant - 6X	00:08.768
226	SWITCH METALLIC Amplifier Peavey Classic 30 (back of cab) - Click Single Soft - Near - 6X	00:08.768
227	SWITCH METALLIC Amplifier Peavey Classic 30 - Click Single Hard - Distant - 7X	00:14.016
228	SWITCH METALLIC Amplifier Peavey Classic 30 - Click Single Hard - Near - 7X	00:14.016
229	SWITCH METALLIC Amplifier Peavey Classic 30 - Click Single Soft - Distant - 3X	00:05.754
230	SWITCH METALLIC Amplifier Peavey Classic 30 - Click Single Soft - Near - 3X	00:05.754
231	SWITCH METALLIC Amplifier Small Dull - Click Single - Distant - 10X	00:15.000
232	SWITCH METALLIC Amplifier Small Dull - Click Single - Near - 10X	00:15.000
233	SWITCH METALLIC Apple iPhone 6 Silent Mode - Click Single - Distant - 7X	00:06.500
234	SWITCH METALLIC Apple iPhone 6 Silent Mode - Click Single - Near - 7X	00:06.500
235	SWITCH METALLIC Generic Small - Click Rapid - Distant - 7X	00:15.000
236	SWITCH METALLIC Generic Small - Click Rapid - Near - 7X	00:15.000
237	SWITCH METALLIC Generic Small - Click Single - Distant - 17X	00:26.500
238	SWITCH METALLIC Generic Small - Click Single - Near - 17X	00:26.500
239	SWITCH METALLIC Gibson Guitar Pickup Strings Ring Out - Click Single - Distant - 2X	00:08.000
240	SWITCH METALLIC Gibson Guitar Pickup Strings Ring Out - Click Single - Near - 2X	00:08.000
241	SWITCH METALLIC Gibson Guitar Pickup - Click Single Hard - Distant - 11X	00:25.500
242	SWITCH METALLIC Gibson Guitar Pickup - Click Single Hard - Near - 11X	00:25.500
243	SWITCH METALLIC Gibson Guitar Pickup - Click Single Soft - Distant - 4X	00:06.000
244	SWITCH METALLIC Gibson Guitar Pickup - Click Single Soft - Near - 4X	00:06.000

Audio Shade - Clicks

245	SWITCH METALLIC Lamp - Click Single Hard - Distant - 5X	00:07.000
246	SWITCH METALLIC Lamp - Click Single Hard - Near - 5X	00:07.000
247	SWITCH METALLIC Lamp - Click Single Soft - Distant - 10X	00:15.000
248	SWITCH METALLIC Lamp - Click Single Soft - Near - 10X	00:15.000
249	SWITCH METALLIC Light Smith Victor SV80 - Click Single - Distant - 24x	00:35.500
250	SWITCH METALLIC Light Smith Victor SV80 - Click Single - Near - 24X	00:35.500
251	SWITCH METALLIC Power Distributor (rack mounted) - Click Single - Distant - 11X	00:16.500
252	SWITCH METALLIC Power Distributor (rack mounted) - Click Single - Near - 11X	00:16.500
253	SWITCH METALLIC Shure A15AS Attenuator - Click Double - Distant - 6X	00:05.683
254	SWITCH METALLIC Shure A15AS Attenuator - Click Double - Near - 6X	00:05.683
255	SWITCH METALLIC Shure A15AS Attenuator - Click Single - Distant - 15X	00:14.464
256	SWITCH METALLIC Shure A15AS Attenuator - Click Single - Near - 15X	00:14.464
257	SWITCH PLASTIC Blender - Click Single Soft - Distant - 12X	00:18.000
258	SWITCH PLASTIC Blender - Click Single Soft - Near - 12X	00:18.000
259	SWITCH PLASTIC Boombox Sony CFS DW-34 AM FM Switch - Click Single Hard - Distant - 6X	00:09.000
260	SWITCH PLASTIC Boombox Sony CFS DW-34 AM FM Switch - Click Single Hard - Near - 6X	00:09.000
261	SWITCH PLASTIC Boombox Sony CFS DW-34 AM FM Switch - Click Single Soft - Distant - 7X	00:10.000
262	SWITCH PLASTIC Boombox Sony CFS DW-34 AM FM Switch - Click Single Soft - Near - 7X	00:10.000
263	SWITCH PLASTIC Box Cutter Knife - Click Single Fast - Distant - 15X	00:22.500
264	SWITCH PLASTIC Box Cutter Knife - Click Single Fast - Near - 15X	00:22.500
265	SWITCH PLASTIC Box Cutter Knife - Click Single Slow - Distant - 17X	00:27.500
266	SWITCH PLASTIC Box Cutter Knife - Click Single Slow - Near - 17X	00:27.500
267	SWITCH PLASTIC Electric Drill A - Click Single - Distant - 12X	00:17.500
268	SWITCH PLASTIC Electric Drill A - Click Single - Near - 12X	00:17.500
269	SWITCH PLASTIC Electric Drill B - Click Single - Distant - 10X	00:10.000
270	SWITCH PLASTIC Electric Drill B - Click Single - Near - 10X	00:10.000
271	SWITCH PLASTIC Hair Trimmer - Click Rapid - Distant - 4X	00:13.500
272	SWITCH PLASTIC Hair Trimmer - Click Rapid - Near - 4X	00:13.500
273	SWITCH PLASTIC Hair Trimmer - Click Single - Distant - 18X	00:18.000
274	SWITCH PLASTIC Hair Trimmer - Click Single - Near - 18X	00:18.000
275	SWITCH PLASTIC Hard-Drive G-Tech (wooden surface) - Click Single Hard - Distant - 7X	00:07.000
276	SWITCH PLASTIC Hard-Drive G-Tech (wooden surface) - Click Single Hard - Near - 7X	00:07.000
277	SWITCH PLASTIC Hard-Drive G-Tech (wooden surface) - Click Single Soft - Distant - 10X	00:15.000
278	SWITCH PLASTIC Hard-Drive G-Tech (wooden surface) - Click Single Soft - Near - 10X	00:15.000
279	SWITCH PLASTIC Intervalometer Canon RS-60E3 - Click Single Hard - Distant - 7X	00:07.000
280	SWITCH PLASTIC Intervalometer Canon RS-60E3 - Click Single Hard - Near - 7X	00:07.000
281	SWITCH PLASTIC Intervalometer Canon RS-60E3 - Click Single Soft - Distant - 8X	00:08.000
282	SWITCH PLASTIC Intervalometer Canon RS-60E3 - Click Single Soft - Near - 8X	00:08.000
283	SWITCH PLASTIC Iron (wooden surface) - Click Rapid - Distant - 3X	00:16.000
284	SWITCH PLASTIC Iron (wooden surface) - Click Rapid - Near - 3X	00:16.000
285	SWITCH PLASTIC Iron (wooden surface) - Click Single - Distant - 22X	00:33.000
286	SWITCH PLASTIC Iron (wooden surface) - Click Single - Near - 22X	00:33.000
287	SWITCH PLASTIC Yamaha PS-270 Keyboard Power On/Off - Click Hard Rapid - Distant - 6X	00:14.000
288	SWITCH PLASTIC Yamaha PS-270 Keyboard Power On/Off - Click Hard Rapid - Near - 6X	00:14.000
289	SWITCH PLASTIC Yamaha PS-270 Keyboard Power On/Off - Click Hard Single - Distant - 8X	00:08.500
290	SWITCH PLASTIC Yamaha PS-270 Keyboard Power On/Off - Click Hard Single - Near - 8X	00:08.500
291	SWITCH PLASTIC Yamaha PS-270 Keyboard Power On/Off - Click Soft Single - Distant - 8X	00:08.000
292	SWITCH PLASTIC Yamaha PS-270 Keyboard Power On/Off - Click Soft Single - Near - 8X	00:08.000
293	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Rapid Struggle - Distant - Long	00:12.094

Audio Shade - Clicks

294	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Rapid Struggle - Near - Long	00:12.094
295	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Single Hard - Distant - 10X	00:14.218
296	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Single Hard - Near - 10X	00:14.218
297	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Single Normal - Distant - 11X	00:15.697
298	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Single Normal - Near - 11X	00:15.697
299	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Single Soft - Distant - 6X	00:08.434
300	SWITCH PLASTIC Shure 588SDX Microphone Power Switch - Click Single Soft - Near - 6X	00:08.434
301	SWITCH PLASTIC Oven Light - Click Single Hard - Distant - 5X	00:07.000
302	SWITCH PLASTIC Oven Light - Click Single Hard - Near - 5X	00:07.000
303	SWITCH PLASTIC Oven Light - Click Single - Distant - 7X	00:07.000
304	SWITCH PLASTIC Oven Light - Click Single - Near - 7X	00:07.000
305	SWITCH PLASTIC Studio Monitor DynAudio BM5AmkII - Click Single Hard - Distant - 6X	00:06.000
306	SWITCH PLASTIC Studio Monitor DynAudio BM5AmkII - Click Single Hard - Near - 6X	00:06.000
307	SWITCH PLASTIC Studio Monitor DynAudio BM5AmkII - Click Single Soft - Distant - 8X	00:08.000
308	SWITCH PLASTIC Studio Monitor DynAudio BM5AmkII - Click Single Soft - Near - 8X	00:08.000
309	SWITCH PLASTIC Surge Protector - Click Rapid - Distant - Long	00:07.000
310	SWITCH PLASTIC Surge Protector - Click Rapid - Near - Long	00:07.000
311	SWITCH PLASTIC Surge Protector - Click Single Hard - Distant - 11X	00:11.000
312	SWITCH PLASTIC Surge Protector - Click Single Hard - Near - 11X	00:11.000
313	SWITCH PLASTIC Surge Protector - Click Single Soft - Distant - 18X	00:17.500
314	SWITCH PLASTIC Surge Protector - Click Single Soft - Near - 18X	00:17.500
315	SWITCH PLASTIC Surge Protector (wooden surface) - Click Rapid - Distant - Long	00:03.976
316	SWITCH PLASTIC Surge Protector (wooden surface) - Click Rapid - Near - Long	00:03.976
317	SWITCH PLASTIC Surge Protector (wooden surface) - Click Single Hard - Distant - 10X	00:10.000
318	SWITCH PLASTIC Surge Protector (wooden surface) - Click Single Hard - Near - 10X	00:10.000
319	SWITCH PLASTIC Surge Protector (wooden surface) - Click Single Soft - Distant - 13X	00:19.000
320	SWITCH PLASTIC Surge Protector (wooden surface) - Click Single Soft - Near - 13X	00:19.000
321	BUTTON PLASTIC Bicycle 6KU Gear Shifter Down - Click Single Hard - Distant - 9X	00:18.000
322	BUTTON PLASTIC Bicycle 6KU Gear Shifter Down - Click Single Hard - Near - 9X	00:18.000
323	BUTTON PLASTIC Bicycle 6KU Gear Shifter Down - Click Single Soft - Distant - 8X	00:16.000
324	BUTTON PLASTIC Bicycle 6KU Gear Shifter Down - Click Single Soft - Near - 8X	00:16.000
325	BUTTON PLASTIC Bicycle 6KU Gear Shifter Up - Click Burst Hard - Distant - 4X	00:08.000
326	BUTTON PLASTIC Bicycle 6KU Gear Shifter Up - Click Burst Hard - Near - 4X	00:08.000
327	BUTTON PLASTIC Bicycle 6KU Gear Shifter Up - Click Single Hard - Distant - 5X	00:10.000
328	BUTTON PLASTIC Bicycle 6KU Gear Shifter Up - Click Single Hard - Near - 5X	00:10.000
329	BUTTON PLASTIC Bicycle 6KU Gear Shifter Up - Click Single Soft - Distant - 9X	00:18.500
330	BUTTON PLASTIC Bicycle 6KU Gear Shifter Up - Click Single Soft - Near - 9X	00:18.500
331	SWEETENER METALLIC Bicycle 6KU Wheel - Click Spin Fast Ramp Down Long - Distant - 3X	03:35.074
332	SWEETENER METALLIC Bicycle 6KU Wheel - Click Spin Fast Ramp Down Long - Near - 3X	03:35.074
333	SWEETENER METALLIC Bicycle 6KU Wheel - Click Spin Steady Crank Various - Distant - 7X	00:48.901
334	SWEETENER METALLIC Bicycle 6KU Wheel - Click Spin Steady Crank Various - Near - 7X	00:48.901
335	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Back Space Single - Contact - 10X	00:21.608
336	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Back Space Single - Distant - 10X	00:21.608
337	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Back Space Single - Near - 10X	00:21.608
338	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Letter Single - Contact - 15X	00:36.666
339	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Letter Single - Distant - 15X	00:36.666
340	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Letter Single - Near - 15X	00:36.666
341	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Space Bar Single - Contact - 6X	00:15.000
342	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Space Bar Single - Distant - 6X	00:15.000

Audio Shade - Clicks

343	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Click Space Bar Single - Near - 6X	00:15.000
344	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Type Normal Operation - Contact - Long	01:44.283
345	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Type Normal Operation - Distant - Long	01:44.283
346	BUTTON METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Type Normal Operation - Near - Long	01:44.283
347	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Bell Ring Single - Distant - 5X	00:17.500
348	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Bell Ring Single - Near - 5X	00:17.500
349	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Load Paper - Contact - 1X	00:06.376
350	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Load Paper - Distant - 1X	00:06.376
351	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Load Paper - Near - 1X	00:06.376
352	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Load Remove Paper - Contact - 2X	00:31.039
353	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Load Remove Paper - Distant - 2X	00:31.039
354	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Load Remove Paper - Near - 2X	00:31.039
355	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Return Slide Back with Bell - Contact - 3X	00:13.068
356	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Return Slide Back with Bell - Distant - 3X	00:13.068
357	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Return Slide Back with Bell - Near - 3X	00:13.068
358	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Return Slide Back - Contact - 8X	00:36.757
359	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Return Slide Back - Distant - 8X	00:36.757
360	SWEETENER METALLIC Typewriter Underwood Portable 1926 (on wooden desk) - Return Slide Back - Near - 8X	00:36.757
361	SWEETENER METALLIC Stapler Broken Small Ring Out - Click Various - Distant - 27X	00:46.000
362	SWEETENER METALLIC Stapler Broken Small Ring Out - Click Various - Near - 27X	00:46.000
363	SWEETENER METALLIC WEAPON AK-47 Gun Bolt - Cock Rapid - Near	00:03.532
364	SWEETENER METALLIC WEAPON AK-47 Gun Bolt - Cock Single - Near - 11X	00:21.306
365	SWEETENER METALLIC XLR Cable - Click Connect Fast Single - Distant - 5X	00:06.635
366	SWEETENER METALLIC XLR Cable - Click Connect Fast Single - Near - 5X	00:06.635
367	SWEETENER METALLIC XLR Cable - Click Connect Slow Single - Distant - 2X	00:02.187
368	SWEETENER METALLIC XLR Cable - Click Connect Slow Single - Near - 2X	00:02.187
369	SWEETENER PLASTIC Electric Drill Battery - Click Remove/Insert - Distant - 11X	00:40.768
370	SWEETENER PLASTIC Electric Drill Battery - Click Remove/Insert - Near - 11X	00:40.768
371	SWEETENER PLASTIC Memory Card Reader - Click Single Open Shut - Distant - 9X	00:25.500
372	SWEETENER PLASTIC Memory Card Reader - Click Single Open Shut - Near - 9X	00:25.500
373	SWEETENER METALLIC Door Deadbolt (prop) - Click Retract Sharp Single - Distant - 9X	00:08.688
374	SWEETENER METALLIC Door Deadbolt (prop) - Click Retract Sharp Single - Near - 9X	00:08.688
375	SWEETENER METALLIC Door Knob Bolt Mechanism (prop) - Turn Latch Lock Slow Single - Distant	00:19.000
376	SWEETENER METALLIC Door Knob Bolt Mechanism (prop) - Turn Latch Lock Slow Single - Near	00:19.000
377	SWEETENER METALLIC Door Knob Lock (prop) - Latch Slick Single - Distant - 3X	00:02.869
378	SWEETENER METALLIC Door Knob Lock (prop) - Latch Slick Single - Near - 3X	00:02.869
379	SWEETENER METALLIC Door Knob Mechanism Lock (prop) - Latch Clunky Single - Distant - 5X	00:05.000
380	SWEETENER METALLIC Door Knob Mechanism Lock (prop) - Latch Clunky Single - Near - 5X	00:05.000
381	SWEETENER METALLIC Door Knob Mechanism (prop) - Click Latch Turn Lock Dull Fast Single - Distant - 23X	00:34.000
382	SWEETENER METALLIC Door Knob Mechanism (prop) - Click Latch Turn Lock Dull Fast Single - Near - 23X	00:34.000
383	SWEETENER METALLIC Door Knob Mechanism (prop) - Rotate Click Fast Single - Distant - 6X	00:09.500
384	SWEETENER METALLIC Door Knob Mechanism (prop) - Rotate Click Fast Single - Near - 6X	00:09.500
385	SWEETENER METALLIC Door Knob Mechanism (prop) - Rotate Rattle Single - Distant - 37X	00:57.551
386	SWEETENER METALLIC Door Knob Mechanism (prop) - Rotate Rattle Single - Near - 37X	00:57.551
387	SWEETENER METALLIC Door Knob Mechanism (prop) - Slide Bright Lock Single - Distant - 19X	00:20.000
388	SWEETENER METALLIC Door Knob Mechanism (prop) - Slide Bright Lock Single - Near - 19X	00:20.000
389	SWEETENER METALLIC Door Knob Parts (prop) - Impact Bright Rattle Single - Distant - 4X	00:03.820
390	SWEETENER METALLIC Door Knob Parts (prop) - Impact Bright Rattle Single - Near - 4X	00:03.820
391	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Insert Loose Single - Distant - 10X	00:17.319

Audio Shade - Clicks

392	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Insert Loose Single - Near - 10X	00:17.319
393	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Rattle Loose Soft Single - Distant - 6X	00:10.593
394	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Rattle Loose Soft Single - Near - 6X	00:10.593
395	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Rattle Tight Hard Single - Distant - 8X	00:10.216
396	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Rattle Tight Hard Single - Near - 8X	00:10.216
397	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Tonal Single - Distant - 4X	00:04.037
398	SWEETENER METALLIC Door Knob Parts (prop) - Impact Clank Tonal Single - Near - 4X	00:04.037
399	SWEETENER METALLIC Door Knob Parts (prop) - Impact Rattle Ring Out Single - Distant - 10X	00:10.362
400	SWEETENER METALLIC Door Knob Parts (prop) - Impact Rattle Ring Out Single - Near - 10X	00:10.362
401	SWEETENER METALLIC Door Knob Parts (prop) - Lock Twist Rattle Loose Single - Distant - 26X	00:26.664
402	SWEETENER METALLIC Door Knob Parts (prop) - Lock Twist Rattle Loose Single - Near - 26X	00:26.664
403	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Bright Burst Single - Distant - 19X	00:27.930
404	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Bright Burst Single - Near - 19X	00:27.930
405	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Jingle Handling Hard Aggressive Steady - Distant - Long	00:05.210
406	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Jingle Handling Hard Aggressive Steady - Near - Long	00:05.210
407	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Handling Steady With Lock at End - Distant - Long	00:04.813
408	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Handling Steady With Lock at End - Near - Long	00:04.813
409	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Jingle Handling Soft Steady - Distant - Long	00:16.460
410	SWEETENER METALLIC Door Knob Parts (prop) - Rattle Jingle Handling Soft Steady - Near - Long	00:16.460
411	SWEETENER METALLIC Door Knob Parts (prop) - Rotate Rattle Fast Steady - Distant - Long	00:07.516
412	SWEETENER METALLIC Door Knob Parts (prop) - Rotate Rattle Fast Steady - Near - Long	00:07.516
413	SWEETENER METALLIC Door Knob Parts (prop) - Rotate Rattle Ring Out Single - Distant - 7X	00:12.500
414	SWEETENER METALLIC Door Knob Parts (prop) - Rotate Rattle Ring Out Single - Near - 7X	00:12.500
415	SWEETENER METALLIC Door Knob Parts (prop) - Shift Rattle Movement Single - Distant - 22X	00:25.138
416	SWEETENER METALLIC Door Knob Parts (prop) - Shift Rattle Movement Single - Near - 22X	00:25.138
417	SWEETENER METALLIC Oven Door - Shut Hard Single - Contact - 4X	00:15.466
418	SWEETENER METALLIC Oven Door - Shut Hard Single - Distant - 4X	00:15.466
419	SWEETENER METALLIC Oven Door - Shut Hard Single - Near - 4X	00:15.466
420	SWEETENER METALLIC Oven Door - Shut Soft Single - Contact - 5X	00:14.532
421	SWEETENER METALLIC Oven Door - Shut Soft Single - Distant - 5X	00:14.532
422	SWEETENER METALLIC Oven Door - Shut Soft Single - Near - 5X	00:14.532
423	SWEETENER METALLIC Oven Drawer - Open Shut Hard Single - Contact - 7X	00:21.356
424	SWEETENER METALLIC Oven Drawer - Open Shut Hard Single - Distant - 7X	00:21.356
425	SWEETENER METALLIC Oven Drawer - Open Shut Hard Single - Near - 7X	00:21.356
426	SWEETENER METALLIC Oven Drawer - Open Shut Soft Single - Contact - 14X	00:37.754
427	SWEETENER METALLIC Oven Drawer - Open Shut Soft Single - Distant - 14X	00:37.754
428	SWEETENER METALLIC Oven Drawer - Open Shut Soft Single - Near - 14X	00:37.754
429	SWEETENER METALLIC Oven Drawer - Shut Slam Hard Single - Contact - 7X	00:24.014
430	SWEETENER METALLIC Oven Drawer - Shut Slam Hard Single - Distant - 7X	00:24.014
431	SWEETENER METALLIC Oven Drawer - Shut Slam Hard Single - Near - 7X	00:24.014
432	SWEETENER METALLIC Oven - Impact Hand Hard Single - Contact - 4X	00:14.793
433	SWEETENER METALLIC Oven - Impact Hand Hard Single - Distant - 4X	00:14.793
434	SWEETENER METALLIC Oven - Impact Hand Hard Single - Near - 4X	00:14.793
435	SWEETENER METALLIC Oven - Impact Hand Soft Single - Contact - 9X	00:32.897
436	SWEETENER METALLIC Oven - Impact Hand Soft Single - Distant - 9X	00:32.897
437	SWEETENER METALLIC Oven - Impact Hand Soft Single - Near - 9X	00:32.897